

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



Diameter: 8 in
Height: 2.5 in (does not include bulb)
Overall Ht. W/Stem And Swivel: 59 in

P500392-109 Trimble

Trimble Collection One-Light Brushed Bronze Mini Pendant

Category: Pendants

Finish: Brushed Bronze (Plated) with Matte Black accent

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
with quick link		Incandescent: 60-watt MAX per socket	
One 6", four 12" lengths of stem included		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	