

Project:	
Fixture Type:	
Location:	
Contact:	

P500394-009 Trimble

Trimble Collection One-Light Brushed Nickel Pendant

Category: Pendants

Finish: Brushed Nickel (Plated) with Graphite accent

Construction: Steel Construction **Glass/Shade:** Etched Glass Bell



Diameter: 18 in Height: 7-1/4 in

Overall Ht. W/Chain And Stem: 72 in

Etched Glass Bell Width: 6-3/8 in Height: 4-3/4 in

		Height. 4-3/4 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included		Incandescent: 100-watt MAX per	, and the second
Six links of 9 Gauge chain supplied with quick link		LED: 17.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.18" W., 0.81" ht., 5.18" depth			