

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500396-201 Cordova

Cordova Collection Medium One-Light Natural Rattan Organic Modern Pendant with White Linen Shade

Category: Pendants

Finish: Natural Rattan (Unfinished)

Construction: Steel Construction

Glass/Shade: White Linen Fabric Round



Diameter: 16 in
Height: 10 in
Overall Ht. W/Cord: 119.5 in

White Linen Fabric Round
Width: 16 in
Height: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	