

Project:
Fixture Type:

Location:
Contact:

P500400-009 Silva

Silva Collection Three-Light Brushed Nickel White Linen Shade Pendant

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction

0.87" ht., 5.12" depth

Glass/Shade: White Linen Fabric Round Shade, Fabric Linen Round Shade



Diameter: 22 in Height: 9-5/8 in

Overall Ht. W/Chain And Stem: 75 in

White Linen Fabric Round Shade

Width: 17-1/4 in Height: 2-5/8 in

Fabric Linen Round Shade

Width: 17-1/4 in Height: 6-7/8 in

		Height. 6-7/8 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included Six links of 9 Gauge chain		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
supplied with quick link			
		Fully dimmable with dimmable	
One 6", four 12" lengths of stem included		bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W.,			