

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500401-196 Burgess

Burgess Collection One-Light Aged Bronze Modern Farmhouse Pendant

**Category:** Pendants

**Finish:** Aged Bronze (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Seeded Glass Cylindrical



Diameter: 9-1/2 in  
Height: 12-3/8 in  
Overall Ht. W/Chain And Stem: 77-1/2 in

Clear Seeded Glass Cylindrical  
Width: 5 in  
Height: 10-7/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth			