

Project:

Fixture Type:

Location:

Contact:

P500401-31M

Burgess

Burgess Collection One-Light Matte Black Modern Farmhouse Pendant

Category: Pendants Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 9-1/2 in Height: 12-3/8 in

Overall Ht. W/Chain And Stem: 77-1/2 in

Clear Seeded Glass Cylindrical

Width: 5 in Height: 10-7/16 in

	Height. 10 //10 m		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
S.I.a.i.	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included		Incandescent: 60-watt MAX per	
Six links of 9 Gauge chain supplied with quick link		LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth			