

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500402-196 Burgess

Burgess Collection Five-Light Aged Bronze Modern Farmhouse Hall & Foyer Light

Category: Hall & Foyer
Finish: Aged Bronze (Painted)
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 15-1/2 in
Height: 23-5/8 in
Overall Ht. W/Chain And Stem: 89 in

Clear Seeded Glass Cylindrical
Width: 3-15/16 in
Height: 6-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(5) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth			