

Project:			
Fixture Type:			
Location:			
Contact:			

P500402-31M

Burgess

Burgess Collection Five-Light Matte Black Modern Farmhouse Hall & Foyer Light

Category: Hall & Foyer Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 15-1/2 in Height: 23-5/8 in

Overall Ht. W/Chain And Stem: 89 in

Clear Seeded Glass Cylindrical

Width: 3-15/16 in Height: 6-5/16 in

		0 21	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(5) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included		Incandescent: 60-watt MAX per	
Six links of 9 Gauge chain supplied with quick link		LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem		Fully dimmable with dimmable bulbs	
included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth			