

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |
| | | |

Contact:

P500403-163

Cofield

Cofield Collection One-Light Vintage Brass Transitional Pendant

Category: Pendants

Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Diameter: 4 in Height: 9-3/4 in

Overall Ht. W/Cord: 138-1/2 in

Clear Glass Cylindrical

Width: 4 in Height: 8-1/2 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--------------------------|--|---------------------------|
| Ceiling Cord | 10 feet of wire supplied | (1) Medium Base (E26) Socket | cULus Dry Location Listed |
| Mounting plate for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| One 8" lengths of stem included | | Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket | |
| Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth | | Fully dimmable with dimmable bulbs | |