

Project:			
Fixture Type:			
Location:			
Contact:			

P500404-009

Cofield

Cofield Collection One-Light Brushed Nickel Transitional Pendant

Category: Pendants

Finish: Brushed Nickel (Plated) **Construction:** Steel Construction

Glass/Shade: Etched White Glass Cylindrical



Diameter: 4 in Height: 9-3/4 in

Overall Ht. W/Cord: 138-1/2 in

Etched White Glass Cylindrical

Width: 4 in Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 8" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		Fully dimmable with dimmable bulbs	