PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P500404-163 Cofield

Cofield Collection One-Light Vintage Brass Transitional Pendant

Category: Pendants Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Etched White Glass Cylindrical



Diameter: 4 in Height: 9-3/4 in Overall Ht. W/Cord: 138-1/2 in

Etched White Glass Cylindrical Width: 4 in Height: 8-1/2 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--------------------------|--|---------------------------|
| Ceiling Cord | 10 feet of wire supplied | (1) Medium Base (E26) Socket | cULus Dry Location Listed |
| Mounting plate for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| One 8" lengths of stem included | | Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket | |
| Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth | | Fully dimmable with dimmable bulbs | |