

Project:		
Fixture Type:		
Location:		

Contact:

dant

P500405-009 Garris

Garris Collection One-Light Brushed Nickel Clear Glass Transitional Mini-Pen-

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl,



Diameter: 8 in Height: 8-1/4 in

Overall Ht. W/Cord: 128.5 in

Clear Glass Bowl Width: 8 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
10 feet of cord		socket	
		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4"			
recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		Fully dimmable with dimmable bulbs	