

Project:			
Fixture Type:			
Location:			
Contact:			

P500409-009

Copeland

Copeland Collection One-Light Brushed Nickel Mid-Century Modern Pendant

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Cone



Diameter: 10 in Height: 11-1/2 in

Overall Ht. W/Stem: 68 in

Etched Opal Glass Cone

Width: 10 in Height: 10 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 75-watt MAX per	
One 6", four 12" lengths of stem		socket	
included		LED: 15-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	