PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P500409-31M Copeland

Copeland Collection One-Light Matte Black Mid-Century Modern Pendant

Category: Pendants Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Etched Opal Glass Cone



Diameter: 10 in Height: 11-1/2 in Overall Ht. W/Stem: 68 in

Etched Opal Glass Cone Width: 10 in Height: 10 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	