

Project:

Fixture Type:

Location:

Contact:

## P500410-31M

## Goodwin

Goodwin Collection One-Light Matte Black Modern Farmhouse Pendant

Category: Pendants
Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: White Linen Fabric Cylindrical



Diameter: 7 in Height: 16-3/4 in

Overall Ht. W/Chain And Stem: 83 in

White Linen Fabric Cylindrical

Width: 7 in Height: 8-1/16 in

		0 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	96 in of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included		Incandescent: 60-watt MAX per	<b>,</b>
Six links of 9 Gauge chain supplied with quick link		LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth			