

Project:			
Fixture Type:			
Location:			
Contact:			

P500411-009

Goodwin

Goodwin Collection Four-Light Brushed Nickel Modern Farmhouse Hall & Foyer Light

 $\textbf{Category:} \ \mathsf{Hall} \ \& \ \mathsf{Foyer}$

Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Diameter: 14 in Height: 20-1/2 in

Overall Ht. W/Chain: 71-1/2 in

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	