

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500418-161 Lattimore

Lattimore Collection Three-Light Aged Brass Hall & Foyer Light

**Category:** Hall & Foyer

**Finish:** Aged Brass (Painted) with Weathered Rattan accent

**Construction:** Steel Construction



Diameter: 16 in  
Height: 20-1/2 in  
Overall Ht. W/Chain: 95-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 2.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	