

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500422-31M Saucedo

Saucedo Collection Five-Light Matte Black Modern Pendant

Category: Pendants

Finish: Matte Black (Painted)

Construction: Steel Construction



Diameter: 24.5 in
Height: 22 in
Overall Ht. W/Stem And Swivel: 78.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	