

Project:		
Fixture Type:		
Location:		
Contact:		

P500430-31M Clarion

Clarion Collection One-Light Matte Black Etched White Transitional Pendant

Category: Pendants

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Bell



Diameter: 10.5 in Height: 15-7/8 in

Overall Ht. W/Stem And Swivel: 72.5 in

Etched Opal Glass Bell Width: 10.5 in Height: 15-1/8 in

		<u> </u>	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	