

Project:			
Fixture Type:			
Location:			
Contact:			

P500433-009 Vertex

 $\label{thm:contemporary} \mbox{Vertex Collection One-Light Brushed Nickel Etched White Contemporary} \\ \mbox{Foyer Light}$

Category: Hall & Foyer Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Etched White Glass Cylindrical



Square: 12 in Height: 22.5 in

Overall Ht. W/Chain: 73.5 in

Etched White Glass Cylindrical

Width: 5-1/8 in Height: 10-1/16 in

		8 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
48 in of 9 Gauge chain supplied		socket	
with quick link		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth		Fully dimmable with dimmable bulbs	