

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500438-31M

Carillon

Carillon Collection One-Light Matte Black Contemporary Pendant

Category: Pendants

Finish: Matte Black (Painted)

Construction: Steel Housing

Glass/Shade: Clear Glass Bell, Opal Glass Bell



Diameter: 9-7/8 in
Height: 14-1/4 in
Overall Ht. W/Stem And Swivel: 70-1/2 in

Clear Glass Bell
Width: 9-7/8 in
Height: 13-3/8 in

Opal Glass Bell
Width: 5-1/8 in
Height: 7-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	96 in of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth			