PROGRESS LIGHTING[®]

Project:

Fixture Type:

Location:

Contact:

P500440-163 Hillcrest

HillIcrest Collection Four-Light Vintage Brass Transitional Hall & Foyer Light

Category: Hall & Foyer Finish: Vintage Brass (Plated) Construction: Steel Housing Glass/Shade: Clear Tempered Glass Flat Panels



Square: 13 in Height: 22 in Overall Ht. W/Chain: 73 in

Clear Tempered Glass Flat Panels Width: 0-3/16 in Height: 15-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs.	