

Project:

Fixture Type:

Location:

Contact:

P500441-009

Hillcrest

HillIcrest Collection Four-Light Brushed Nickel Transitional Hall & Foyer Light

Category: Hall & Foyer

Finish: Brushed Nickel (Plated)
Construction: Steel Housing

Glass/Shade: Clear Tempered Glass Flat Panels



Square: 17 in Height: 29-3/4 in Overall Ht. W/Chain: 81 in

Clear Tempered Glass Flat Panels

Width: 0-3/16 in Height: 16 in

		8	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.75" ht., 4.5" depth		bulbs.	