

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P500441-163
Hillcrest

Hillcrest Collection Four-Light Vintage Brass Transitional Hall & Foyer Light

Category: Hall & Foyer
Finish: Vintage Brass (Plated)
Construction: Steel Housing
Glass/Shade: Clear Tempered Glass Flat Panels



Square: 17 in
 Height: 29-3/4 in
 Overall Ht. W/Chain: 81 in

Clear Tempered Glass Flat Panels
 Width: 0-3/16 in
 Height: 16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.75" ht., 4.5" depth			