

Project: Fixture Type: Location: Contact:



P500442-204 Loretta

Loretta Collection Three-Light Gold Ombre Transitional Pendant

Category: Pendants

Finish: Gold Ombre (Hand Painted) Construction: Steel Housing Glass/Shade: Clear Glass Round

Diameter: 18 in

Height: 13-1/2 in Overall Ht. W/Chain: 66 in

Clear Glass Round Width: 4-5/16 in Height 0-3/4 in

	Height: 0-3/4 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Fixture can be installed as a pendant or semi-flushmount	96 in of wire supplied	(3) Candelabra Base (E12) Socket	cETLus Dry Location Listed
using included hardware	120 VAC	Lamp Type Incandescent: 60-watt MAX per	1-year Limited Warranty
Mounting plate for outlet box included		socket LED: 12.5-watt MAX per socket	
48 in of 9 Gauge square profile chain supplied with quick link		Dimmable to 10% brightness (See Dimming Notes)	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.18" ht., 5.12" depth			