

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P500446-109
Mystic

Mystic Collection One-Light Brushed Bronze Contemporary Pendant

Category: Pendants
Finish: Brushed Bronze (Plated)
Construction: Steel Housing
Glass/Shade: Etched White Glass Cylindrical



Diameter: 14 in
 Height: 10-7/8 in
 Overall Ht. W/Stem And Swivel: 68 in

Etched White Glass Cylindrical
 Width: 4-3/4 in
 Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		Dimmable to 10% brightness (See Dimming Notes)	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth			