

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P500456-31M Seville

Four-Light Pendant

Category: Pendants
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear w/ Vertical Flutes Glass Flat Round

Diameter: 17-7/8 in
 Height: 12-3/4 in
 Overall Ht. W/Chain And Stem: 54 in

Clear w/ Vertical Flutes Glass Flat Round
 Width: 4-3/4 in
 Height: 7-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
6 inches of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", two 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.82" ht., 5.12" depth			