

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P500457-31M Seville

Six-Light Hall & Foyer

Category: Hall & Foyer
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear w/ Vertical Flutes Glass Flat Round

Diameter: 17-7/8 in
 Height: 30 in
 Overall Ht. W/Chain And Stem: 103 in

Clear w/ Vertical Flutes Glass Flat Round
 Width: 4-5/8 in
 Height: 30 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 3 links of chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Americans With Disabilities Act (ADA) compliant
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.82" ht., 5.12" depth			