

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500461-009
Atwell

One-Light Pendant

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: White Glass Round



Diameter: 8 in
Height: 8-1/2 in
Overall Ht. W/Cord: 128-1/2 in

White Glass Round
Width: 8 in
Height: 7-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.06" ht., 5.5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	