

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P500462-009
Atwell

One-Light Pendant

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: White Glass Round



Diameter: 10 in
 Height: 10-1/2 in
 Overall Ht. W/Cord: 130-1/2 in

White Glass Round
 Width: 10 in
 Height: 9-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.06" ht., 5.5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	