

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P500462-31M**  
**Atwell**

One-Light Pendant

**Category:** Pendants  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** White Glass Round



Diameter: 10 in  
Height: 10-1/2 in  
Overall Ht. W/Cord: 130-1/2 in

White Glass Round  
Width: 10 in  
Height: 9-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.06" ht., 5.5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	