

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



**P500482-191**  
**Stanza**

Stanza Collection One-Light Brushed Gold New Traditional Pendant Light

**Category:** Pendants

**Finish:** Brushed Gold (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Opal Ribbed Glass Bell

Diameter: 10-1/4 in  
Height: 21 in  
Overall Ht. W/Chain And Stem: 82-1/2 in

Etched Opal Ribbed Glass Bell  
Width: 10-1/4 in  
Height: 13-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	96 in of wire supplied	(1) Medium Socket	cULus Listed Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
one 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 6" W., 2.5" ht., 6" depth			