

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P500482-31M
Stanza

Stanza Collection One-Light Matte Black New Traditional Pendant Light

Category: Pendants
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Opal Ribbed Glass Bell

Diameter: 10-1/4 in
 Height: 21 in
 Overall Ht. W/Chain And Stem: 82-1/2 in

Etched Opal Ribbed Glass Bell
 Width: 10-1/4 in
 Height: 13-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	96 in of wire supplied	(1) Medium Socket	cULus Listed Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
one 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 6" W., 2.5" ht., 6" depth			