

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P5170-104 Replay

One-light mini-pendant from the Replay Collection, feature smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look. Polished Nickel finish.

- Smooth forms and linear details.
- Pleasingly elegant frame.
- Simplified modern look.
- Includes one 6", four 12" stems and 6 links of chain.

Category: Pendants

Finish: Polished Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched Outside, Painted White Inside glass Shade



Diameter: 3-7/8 in
Height: 6-1/16 in
Overall Ht. W/Stem: 72 in

Etched Outside, Painted White Inside glass Shade
Width: 3-7/8 in
Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain	Prewired	Quantity: One 100 W max. Medium Base or LED equivalent	UL-CUL Dry Location Listed
Mounting strap for outlet box included	10 feet of wire supplied	E26 base porcelain socket	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V		
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.875" ht., 5" depth			