

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P5173-74
Archie

Archie Collection One-Light Venetian Bronze Double Prismatic Glass Coastal Mini-Pendant Light

Category: Pendants
Finish: Venetian Bronze (Plated)
Construction: Steel Construction
Glass/Shade: Double Prismatic Glass Shade



Diameter: 5-3/4 in
 Height: 8-3/4 in
 Overall Ht. W/Stem: 75 in

Double Prismatic Glass Shade
 Width: 5-3/4 in
 Height: 4-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	Prewired	(1) Medium Base (E26) socket	UL-CUL Dry Location Listed
Mounting strap for outlet box included	10 feet of wire supplied	Lamp Type A-19	1-year Limited Warranty
six links of 9 gauge chain supplied	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
two 6", one 12", two 15" lengths of stem included		Fully dimmable with dimmable bulbs.	
canopy covers a standard 4" recessed outlet box: 5.125" W., 1" ht., 5.125" depth			