

Simple LED

Ceiling cord Mounted • Dry Location Listed PROGRESS LED



Description:

One-light cord-hung pendant with an LED source that is neatly tucked inside a frosted acrylic shade. A light commercial pendant ideal for restaurants, bar and hotel applications. Brushed Nickel finish.

Specifications:

- White polystyrene Shade
- White acrylic Diffuser
- Light commercial LED pendant.
- Frosted acrylic shade.
- Ideal for restaurants, bar and hotel applications.
- Dimmable to 10% with many ELV dimmers
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 1.0625 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	405/54 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Dry Location Listed ENERGY STAR® qualified


P5176-0930K9



Dimensions:

Diameter: 5-7/8 in
Height: 8-5/8 in
Overall Ht. W/Cord: 130 in

White polystyrene Shade
Width: 5-13/16 in



Photometrics:


P5176-0930K9

ELECTRICAL DATA	P5176-0930K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.075 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P5176-0930K9
 LED Light Engine: 3000 K 90 CRI
 System Wattage: 9
 Fixture delivered lumens: 405
 Fixture Efficacy: 54
 Spacing Criteria: 0.9

CANDELA DISTRIBUTION		
DEG	CANDELA	LUMENS
0	187	
5	186	18
15	181	51
25	129	59
35	58	38
45	39	30
55	31	27
65	26	25
75	22	23
85	20	21
90	19	
95	19	21
105	20	21
115	20	20
125	19	17
135	18	14
145	16	10
155	14	6
165	10	3
175	1	0
180	0	

ZONAL LUMEN SUMMARY		
ZONE	LUMENS	%FIXT
0-30	127	31.4
0-40	165	40.8
0-60	223	55.0
0-90	293	72.3
90-120	62	15.2
90-130	79	19.4
90-150	103	25.3
90-180	112	27.7
0-180	405	100.0



Test 15.01356 Test Date 7/28/15



P5176-0930K9

Dimming Notes:

P5176-0930K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron Nova T NTELV-300

Lutron Verti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.