

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Halogen

P5186-104WB

Fun and flirty one-light metal shade mini-pendant gives a hint of light. White gloss interior for optimal light output. Ideal for a variety of interiors. Includes one 50w MR16 GU10 lamp.

- Fun and flirty one-light metal shade mini-pendant
- White gloss interior for optimal light output.
- Includes one 50w MR16 GU10 lamp.
- Polished Nickel finish
- Includes two 6", one 12", two 15" stems and 6 links of chain

Category: Pendants

Finish: Polished Nickel (plated)

Construction: Steel Construction

Glass/Shade: Metal shade



Diameter: 5-1/8"

Height: 5-7/8"

Overall Ht. W/Stem: 72"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied Two 6", one 12", two 15" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 50w max. MR-16 (GU10, 120V)(included) GU10 base socket	cCSAus Dry location listed 1 year warranty