

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5199-12

Markor

This versatile modular pendant stem kit system will help to make installation simple. The stem kit allows you to customize lighting to perfectly fit the personality of your home. A satin brass finish coats this pendant stem kit system.

- Customize lighting to perfectly fit the personality of your home.
- Easy installation.
- Coated in a satin brass finish.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, transitional, modern, or contemporary settings.
- Measures 4-3/4-inch width by 6-1/4-inch height.
- Uses three medium base bulbs that are sold separately (100w max - LED, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Satin Brass (Plated)

Construction: Steel Construction



Diameter: 4-3/4"
Height: 6-1/4"
Overall Ht. W/Stem: 68"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting Mounting Strap for outlet box included	10 feet of wire supplied	Three 100w max. Medium Base or LED equivalent	1-year Limited Warranty
Two 6", two 15" lengths of stem included	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" octagonal recessed outlet box			
Canopy: 5.68" W., 1.43" ht., 5.68" depth			