

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P5199-31

## Markor

This versatile modular pendant stem kit system will help to make installation simple. The stem kit allows you to customize lighting to perfectly fit the personality of your home. A black finish coats this pendant stem kit system.

- Customize lighting to perfectly fit the personality of your home.
- Easy installation.
- Coated in a black finish.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, transitional, modern, or contemporary settings.
- Measures 4-3/4-inch width by 6-1/4-inch height.
- Uses three medium base bulbs that are sold separately (100w max - LED, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Pendants

**Finish:** Black (Painted)

**Construction:** Steel Construction



**Diameter:** 4-3/4"  
**Height:** 6-1/4"  
**Overall Ht. W/Stem:** 68"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting Mounting Strap for outlet box included	10 feet of wire supplied	Three 100w max. Medium Base or LED equivalent	1-year Limited Warranty
Two 6", two 15" lengths of stem included	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" octagonal recessed outlet box			
Canopy: 5.68" W., 1.43" ht., 5.68" depth			