

Project:			
Fixture Type:			
Location:			
Contact:			

P540004-031

Gibbes Street

Incorporate a flawless lighting experience that fills your home with an understated elegance and rustic charm with this post lantern. This farmhouse-inspired masterpiece cradles clear beveled glass panes just right for offering a warm, welcoming glow to your friends and family. A traditional lantern frame with a beautiful black finish houses the light bases in this timeless design.

- This farmhouse-inspired masterpiece cradles clear beveled glass panes just right for offering a warm, welcoming glow to your friends and family.
- A traditional lantern frame with a beautiful black finish houses the light bases in this timeless design.
- Incorporate a flawless lighting experience that fills your home with an understated elegance and rustic charm with this post lantern.
- · Ideal for any outdoor space in need of illumination.
- · Perfect for any transitional or new traditional setting.
- · Measures 9-1/2-inch width by 26-7/8-inch height.
- \cdot Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Post mounted, fits standard 3" post (sold separately)
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Cast Aluminum Construction **Glass/Shade:** Clear Beveled glass Panel



Square: 9-1/2 in Height: 26-7/8 in

Clear Beveled glass Panel Width: 8-1/16 in Height: 16-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	Prewired	Quantity: Three 60 W max. Candelabra	CCSAus Wet Location Listed
	6 inches of wire supplied	Base or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	