

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P540017-108 Janssen

Create a home full of modern elegance with this contemporary post lantern. A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest. The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.

- The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.
- A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest.
- Create a home full of modern elegance with this contemporary post lantern.
- Ideal for any outdoor space in need of illumination.
- Perfect for modern or contemporary styles.
- Measures 7-1/2-inch width by 20-5/8-inch height.
- Post mounted, fits standard 3" post (sold separately)
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Outdoor

**Finish:** Oil Rubbed Bronze (Painted)

**Construction:** Aluminum Construction

**Glass/Shade:** Etched glass Cylindrical Shade



Diameter: 7-1/2 in  
Height: 20-5/8 in

Etched glass Cylindrical Shade  
Width: 4-1/2 in  
Height: 12 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	Prewired 6 inches of wire supplied 120 V	Quantity: One 100 W max. Medium Base or LED equivalent E26 base Porcelain socket	CCSAus Wet Location Listed 1-year Limited Warranty