

Project:

Fixture Type:

Location:

Contact:

## P540020-31M Gunther

Gunther One-Light Matte Black Modern Farmhouse Post Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Diameter: 8 in Height: 13-1/2 in

Clear Glass Cylindrical Width: 6 in Height: 9-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
post (sold separately)	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per socket	
		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	