## **PROGRESS** LIGHTING<sup>™</sup>

Project: Fixture Type:

Location:

Contact:

## P540024-031 Felton

Achieve the stylish and peaceful home environment you've been waiting for with this beautiful post lantern. The rectangular matte black frame's intelligent design is just right for illuminating any outdoor space in need of illumination. The frame holds elongated, rippled glass panels through which a warm, guiding glow will shine.

- The fixture holds elongated, rippled glass panels through which a warm guiding glow will shine.
- The rectangular matte black frame's intelligent design is just right for illuminating any outdoor space.
- Achieve the stylish and peaceful home environment you've been waiting for with this beautiful post lantern.
- Ideal for any outdoor space in need of illumination.
- $\cdot\,$  Perfect for urban industrial and Craftsman settings.
- Measures 7-1/4-inch width by 18-3/4-inch height.
- Post mounted, fits standard 3" post (sold separately)
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted) Construction: Steel Construction Glass/Shade: Clear Ribbed glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	

-----

Square: 7-1/4 in Height: 18-3/4 in

Clear Ribbed glass Panel Width: 6-1/8 in Height: 16-1/8 in