

Project:

Fixture Type:

Location:

Contact:

## P540046-169

## **Union Square**

Union Square One-Light Antique Copper Urban Industrial Outdoor Post Light

Category: Outdoor

Finish: Antique Copper (Painted) with Matte Black accent

Construction: Steel Construction Glass/Shade: Clear Glass Panel



Length: 9-3/4 in Width: 7 in Height: 26 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per socket	
		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	