

| Project: | | | |
|---------------|--|--|--|
| Fixture Type: | | | |
| Location: | | | |
| C | | | |

P540058-020

Trellis

Create a home that is undeniably beautiful with the intricate craftsmanship of this nature-inspired post lantern. Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes. The panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.

- Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes.
- The glass panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.
- Create a home that is undeniably beautiful with the intricate craftsmanship of this nature-inspired post lantern.
- · Ideal for any entryway, porch, or patio.
- · Perfect for rustic and Craftsman settings.
- · Measures 7-1/2-inch width by 15-3/8-inch height.
- Post mounted, fits standard 3" post (sold separately)
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Antique Bronze (Painted)
Construction: Steel Construction
Glass/Shade: White Art glass Panel



Square: 7-1/2 in Height: 15-3/8 in

White Art glass Panel Width: 5-3/4 in Height: 10-5/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION | |
|---|---------------------------|--|----------------------------|--|
| Post mounted, fits standard 3" post (sold separately) | Prewired | Quantity: One 100 W max. Medium Base or | CCSAus Wet Location Listed | |
| p === (================================ | 6 inches of wire supplied | LED equivalent | 1-year Limited Warranty | |
| | 120 V | E26 base Porcelain socket | | |