

Project:			
Fixture Type:			
Location:			
Contact:			

P540065-031

Benton Harbor

This wall lantern is expertly crafted with that casual, coastal style you love. A clear glass shade shields a simple light base for a seaside-living vibe. The shade is cradled inside an open-cage black frame featuring thin bars and constructed with a non-metallic, corrosion-resistant housing. DURASHIELD by Progress Lighting is built to last. Constructed from a composite polymer material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- · A clear glass shade shields a simple light base for a seaside-living vibe.
- The glass shade is cradled inside an open-cage black frame of corrosion-proof composit polymer.
- The wall lantern is constructed with a non-metallic, corrosion-resistant housing.
- Ideal for any foyer, bedroom, entryway, porch, or patio in transitional or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a
 composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust,
 corrosion, and fading.
- Measures 9-1/8-inch width by 16-3/8-inch height.
- Post mounted, fits standard 3" post (sold separately)
- Uses one medium base bulb that is sold separately (75w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality. }$

Category: Outdoor **Finish:** Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear glass Shade



Diameter: 9-1/8 in Height: 16-3/8 in

Clear glass Shade Width: 7-7/8 in Height: 8-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	Prewired	Quantity: One 75 W max. Medium Base or	CETLus Wet Location Listed
	6 inches of wire supplied	LED equivalent	5-year Limited Warranty
	120 V	E26 base Porcelain socket	