

Project:

Fixture Type:

Location:

Contact:

P540094-31M

Whitmire

Whitmire Collection One-Light Farmhouse Matte Black Clear Seeded Glass Outdoor Post Light

Category: Outdoor

Finish: Matte Black (Painted) with Aged Oak accent

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 7-3/8 in Height: 15-5/8 in

Clear Seeded Glass Cylindrical

Width: 5-1/8 in Height: 11-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per socket	
		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	