



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P540103-030 Cedar Springs

Cedar Springs Collection One-Light Textured Black Gloss Black Metal Shade
 Farmhouse Outdoor Post Lantern

Category: Outdoor
Finish: White (Painted) with Textured Black accent
Construction: Aluminum Construction
Glass/Shade: White Metal Cone



Width: 13-1/4 in
 Extends: 18.5 in
 Height: 17 in

White Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Post Mount	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	Yes, per photometry (not registered with IDA)
		Fully dimmable with dimmable bulbs	