## PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

## **P540104-031** Ramsey

Ramsey Collection Textured Black Modern Farmhouse Post Outdoor Light

Category: Outdoor Finish: Textured Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Panel



Diameter: 9 in Height: 20-7/8 in

| MOUNTING   | ELECTRICAL                | LAMPING                                 | ADDITIONAL INFORMATION     |
|--|---------------------------|---|----------------------------|
| Post mounted, fits standard 3"<br>post (sold separately) | 6 inches of wire supplied | (3) Candelabra Base (E12) Socket        | cCSAus Wet Location Listed |
|  | 120 VAC                   | Lamp Type B10                           | 1-year Limited Warranty    |
|  |                           | Incandescent: 60-watt MAX per<br>socket |                            |
|  |                           | LED: 12.5-watt MAX per socket           |                            |
|  |                           | Fully dimmable with dimmable bulbs      |                            |