

Project:

Fixture Type:

Location:

Contact:

P540107-031

Bradshaw

Bradshaw Collection One-Light Textured Black Clear Glass Transitional Outdoor Post Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Square: 12-3/4 in Height: 25-1/4 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post Top - Fitter For 3" Post Or Pedestal	120 VAC	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
		Lamp Type B10	1-year Limited Warranty
Post Mount			3
		Incandescent: 60-watt MAX per socket	
		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	